

u-sonic 2

Electronic mini cleansing station.



DEEP CLEANSING AND GERM-FREE HYGIENE

For earmolds and hearing protection, germ-free, deep cleansing is important for daily use, personal hygiene and value retention. The new u-sonic 2 is a valuable tool and offers optimal cleansing.

Powerful ultrasound at 40 kHz ensures hygienic cleanliness even with clear water. For intensive cleansing, the addition of a small amount of cleansing concentrate is recommended.

The new u-sonic 2 is particularly suitable for a variety of small parts used in the household, such as jewelry, coins, razors, infant teats, teats as well as prosthetic aids, such as earplugs, braces and much more. Please make sure that the products are ultrasonic cleanable.

THE NEW U-SONIC 2 IS A GOOD CHOICE

The convenience cleaning system provides perfect care for the products to be cleaned, increases their service life, and significantly reduces the risk of failure and repair costs.

Simple handling by pressing the sensor button - everything else runs fully automatically under microprocessor control.

The ultrasound creates millions of tiny energy-charged oxygen bubbles in the liquid. These burst powerfully on the surface of the product and loosen all dirt particles. The result - clinical cleanliness, germs are reduced and thus health risks are minimized.

The new u-sonic 2 offers high benefits. Effective and gentle cleaning and care is the best guarantee for value retention and the long usability of the products.



Perfect
cleansing by
power-ultrasonic



40 kHz
frequency
at 20 watt



Easy handling by
simple touch on
sensor button



100 ml
stainless
steel tub



Automatic turn-off
after 6 min
comfort cleansing



All features
controlled by
microprocessor



Highest product
quality with
2 year warranty



Energy-efficient
and absolutely
safe



100 ML STAINLESS STEEL TANK FOR HYGIENIC CLEANSING

The very high quality stainless steel tank provides optimal space for cleaning the earpieces. Stainless steel tank and powerful piezo transducer produce powerful ultrasound and perfect cleaning effect.

EASY OPERATION VIA SENSOR BUTTON

The u-sonic 2 is switched on simply by touching the sensor button. This innovative technology has many advantages over mechanical buttons, is waterproof and offers more comfort.



REMOVABLE LID FOR FILLING AND EMPTYING

The u-sonic 2 does not need to be filled with water or emptied at the sink. The lid can easily take over this function. The round recess ensures drip-free pouring.

ULTRASONIC TECHNOLOGY FOR PERFECT CLEANSING

Ultrasonic cleaning works on the basis of cavitation. During cavitation, vapor bubbles form in liquids and dissolve again due to pressure fluctuations. This dissolves dirt and other deposits.



NEW STYLISH PACKAGING BUT 100% RECYCLABLE

The new packaging of the u-sonic 2 is not only beautiful to look at and a real highlight on the sales shelf and in the shop window, but made of cardboard 100% recyclable and thus a sign for the environment.